



**LEEFIX FDF**

Fixator for reactive and direct dyes

**Characteristics**

Type of product	Amin aliphatic derivatives
Ionogenity	cationic
Consistency	liquid

**Properties**

- Without any Formaldehyde
- Without any decreasing effect for light fastness
- Any change for color and handle
- Increasing washing fastness
- Useable by pad and exhausted method
- Very suitable for bobbin dyeing
- Compatible with nonionic and cationic softs at dyeing bath
- Decreasing wet blotting

**Application**

Dissolving method    dissolving in water easily

**Guide recipe**

For exhaustion method	1-3 %	Leefix FDF
For pad system	15-30 g/l	Leefix FDF
For printing fabric after washing	3-5 g/l	Leefix FDF
Time	20-30 min	
Temperature	25 °C	
PH	5.5-6.5	

**Special remarks**

Storage stability    12 months